

**Product Name :**  
Motorless Magnetic Stirrer

**Product Code :**  
ELAB-LST0002



## Description :

Motorless Magnetic Stirrer

## Technical Specification :

Direction selector (Clock Wise Counter Clock Wise)

Reset Button

Power ON / OFF switch with fuse protections

Viscosity selector (High Low)

Compact sleek stainless steel housing

Smooth variable speed control

Functional Features:

Speed Control: Step less Variable speed facilitating stirring from 100 900 RPM.

Drive: Motor Less Drive, No wear and tear of moving parts or bearings. Suitable for continuous operation for longer duration.

Re-Set Option: In case the magnetic follower moves off center due to external disturbance to the liquid or shifting of the vessel, the reset button can bring the follower in position and will restart the stirring at the speed set by you.

High / Low Speed Mode: Option of High Speed Mode & Low Speed to select, depending on the viscosity of the solution being stirred.

Heating & Temp. Control: Surface Temperature of Hot Plate

Direction Selection: Allows you the options of stirring clock wise or counter clockwise rotation.

---

# **LAB ENGINEERING**

**Elab Engineering Equipments Manufacturers**